

Leader Light s.r.o. M.Gorkeho 33 SK-052 01 Spisska Nova Ves Slovakia www.leaderlight.eu

SERIAL OUTPUT DATA PROTOCOL

LL IN8-RS0v3 - Potential free contact module

Rev. 0v3

SERIAL FORMAT - 9600 baud, 1 start bit, 8 data bits, 2 stop bits, no parity.

CABLE MANAGEMENT - For RS423 use two-core shielded cable. Shielding=earthing - involved on both sides. RS232 for short distances - you can use a single core shielded cable.

MAXIMUM CABLE LENGTH - RS423 1200m, RS232 100m.

TERMINATION - is not required, but recommended the finish line impedance R = cca.120ohm / 0.6 W

BRANCHING - is not a problem.

HANDSHAKING - is not required - RTS (pin E or 5 on the BBC Micro, or pin 4 to 25 pin "D") and CTS (pin D or 2 on the BBC Micro, or pin 5 to 25 pin "D") must be mutually connected to the computer.

NUMBER OF CHANNELS - according to protocol.

TRANSFER PROTOCOL (label soft on LL IN8-RS: I8 0v3):

Input device (LL IN8-RS) scans eight inputs and sends the following data by ON, HOLDING and OFF the entry:

Broadcast data by Switch ON: I x x O N < CR>
Broadcast data by HOLD: I x x H O < CR>
Broadcast data by Switch OFF: I x x O F < CR>

where: x x - is the number of input 01 - 08

NOTE:

Treatment of inputs is about. 60ms, the command is sent after holding approx.1, 2s.

These informations are subject to change, updates are on: www.leaderlight.eu

SERIAL OUTPUT DATA PROTOCOL

LL IN8-RS0v4 - Potential free contact module

Rev. 0v4

SERIAL FORMAT - 9600 baud, 1 start bit, 8 data bits, 2 stop bits, no parity.

CABLE MANAGEMENT - For RS423 use two-core shielded cable. Shielding=earthing - involved on both sides. RS232 for short distances - you can use a single core shielded cable.

MAXIMUM CABLE LENGTH - RS423 1200m, RS232 100m.

TERMINATION - is not required, but recommended the finish line impedance R = cca.120ohm / 0.6 W

BRANCHING - is not a problem.

HANDSHAKING - is not required - RTS (pin E or 5 on the BBC Micro, or pin 4 to 25 pin "D") and CTS (pin D or 2 on the BBC Micro, or pin 5 to 25 pin "D") must be mutually connected to the computer.

NUMBER OF CHANNELS - according to protocol.

TRANSFER PROTOCOL for E-Cue (label soft on LL IN8-RS: 18 0v4):

Input device (LL IN8-RS) scans eight inputs and sends the following data by ON, HOLDING and OFF the entry:

Broadcast data by Switch ON: Z x x <CR>
Broadcast data by HOLD: D x x <CR>
Broadcast data by Switch OFF: V x x <CR>

where: x x = 11 - 18 (number of input 1 - 8)

NOTE:

Treatment of inputs is about. 60ms, the command is sent after holding approx.1, 2s.

These informations are subject to change, updates are on: www.leaderlight.eu

SERIAL OUTPUT DATA PROTOCOL

LL IN8-RS0v5 - Potential free contact module

Rev. 0v5

SERIAL FORMAT - 9600 baud, 1 start bit, 8 data bits, 2 stop bits, no parity.

CABLE MANAGEMENT - For RS423 use two-core shielded cable. Shielding=earthing - involved on both sides. RS232 for short distances - you can use a single core shielded cable.

MAXIMUM CABLE LENGTH - RS423 1200m, RS232 100m.

TERMINATION - is not required, but recommended the finish line impedance R = cca.120ohm / 0.6 W

BRANCHING - is not a problem.

HANDSHAKING - is not required - RTS (pin E or 5 on the BBC Micro, or pin 4 to 25 pin "D") and CTS (pin D or 2 on the BBC Micro, or pin 5 to 25 pin "D") must be mutually connected to the computer.

NUMBER OF CHANNELS - according to protocol.

TRANSFER PROTOCOL for Creator (label soft on LL IN8-RS: I8 0v5):

Input device (LL IN8-RS) scans eight inputs and sends the following data by ON, HOLDING and OFF the entry:

Broadcast data by Switch ON: I x x O N < CR> K 9 < CR>
Broadcast data by HOLD: I x x H O < CR> K 9 < CR>
Broadcast data by Switch OFF: I x x O F < CR> K 9 < CR>

where: x x = 01 - 08 (number of input 1 - 8)

NOTE:

Treatment of inputs is about. 60ms, the command is sent after holding approx.1, 2s.

These informations are subject to change, updates are on: www.leaderlight.eu